



Finesse™ Quick Install™

Frameless sliding shower door
5375EZ-45

Features

- Frameless.
- 1/4" (6 mm) thick tempered glass.
- CleanCoat® technology creates a protective barrier that repels water, prevents dirt and minerals from collecting, and makes it easier to remove hard water spots.
- Interior and exterior towel bars complete the look of this door.

Material

- Anodized aluminum prevents rust and corrosion.

Technology

- Quick Install system.
- Tempered glass ensures maximum safety and durability.

Installation

- Out-of-plumb adjustability simplifies installation.
- Not for use in hospitality.
- For residential use only.

Included Components

Additional Components:

- Hardware kit
- hex wrench



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Glass Options

Code	Description
------	-------------

Clear


Lake Mist™

DISCONTINUED This product has been discontinued.

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.



Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - 44" (1118 mm)
Min:

Opening Width - 45-1/2" (1156 mm)
Max:

Walk-through - Min: 18-15/16" (481 mm)

Walk-through - Max: 20-7/16" (519 mm)

Glass thickness: 1/4" (6 mm)

Glass coating: CleanCoat®

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 72-5/16" (1837 mm) to allow for installation clearance.