



Finesse™ Quick Install™

Frameless sliding shower door
5375EZ-57

Features

- Frameless.
- 1/4" (6 mm) thick tempered glass.
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)
- Interior and exterior towel bars complete the look of this door.

Material

- Anodized aluminum prevents rust and corrosion.

Technology

- Quick Install system.
- Tempered glass ensures maximum safety and durability.

Installation

- Out-of-plumb adjustability simplifies installation.
- Not for use in hospitality.
- For residential use only.

Included Components

Additional Components:

- Hardware kit
- hex wrench



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Glass Options

Code	Description
	Clear
	Lake Mist™


DISCONTINUED This product has been discontinued.

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

9-24-2021 04:58 - US/CA



Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - 56" (1422 mm)
Min:

Opening Width - 57-1/2" (1461 mm)
Max:

Walk-through - Min: 24-15/16" (633 mm)

Walk-through - Max: 26-7/16" (672 mm)

Glass thickness: 1/4" (6 mm)

Glass coating: CleanCoat®

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 72-5/16" (1837 mm) to allow for installation clearance.