

Features

- Frameless.
- 1/4" (6 mm) thick tempered glass.

Technology

- CleanCoat® nanotechnology provides a smooth, nonstick surface to help prevent buildup of water stains, bacteria and mildew on your glass, to make it easy to clean and keep it looking like new.
- Inside and outside towel bars complete the look of this door.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

Installation

- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:
Hardware kit



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	DR	Deep Bronze
	N	Nickel
	S	Silver

Available Glass Options

Code	Description
	Boxwood™
	Cirkette™
	Clear
	Frosted
	Grafite™
	Lake Mist™
	Oak Park™
	Starscape™



Technical Information

All product dimensions are nominal.

- Installation type: For bath installation
- Opening Width - Min: 54-5/8" (1387 mm)
- Opening Width - Max: 59-5/8" (1514 mm)
- Walk-through - Min: 22-15/16" (583 mm)
- Walk-through - Max: 27-15/16" (710 mm)
- Base-To-Wall Radius 1/2" (13 mm)
 - Max:
- Glass thickness: 1/4" (6 mm)
- Glass coating: CleanCoat®

Notes

- Install this product according to the installation guide.
- The vertical opening should be a minimum of 60-1/2" (1537 mm) to allow for installation clearance.