



# Finesse™ Peak®

Frameless sliding shower door  
**547808-48**

## Features

- Frameless
- 5/16" (8 mm) thick tempered glass
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)
- Vertical blade handles complete the look of this door
- Tempered glass ensures enhanced safety and durability

## Material

- Stainless steel hardware prevents rust and corrosion

## Installation

- Out-of-plumb adjustability simplifies installation
- Not for use in hospitality
- For residential use only



## Codes/Standards









ANSI Z97.1  
CAN/CGSB-12.1  
CPSC 16CFR 1201

## STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	DR	Deep Bronze
	DR	Deep Bronze
	N	Nickel
	N	Nickel
	PBL	Matte Black
	PBL	Matte Black
	S	Silver
	S	Silver

## Available Glass Options


Code	Description
G05	Clear
G03	Frosted

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

3-24-2024 21:01 - US



**Technical Information**

All product dimensions are nominal.

- Base-To-Wall 1/2" (13 mm)
- Radius – Max:
- Shower Ledge Min 2-1/8" (54 mm)
- Flat:
- Shower Wall Min 2-3/8" (60 mm)
- Flat:

**Notes**

Install this product according to the installation guide.

NOTICE: The vertical opening should be a minimum of 72" (1829 mm) to allow clearance for installation.