

Features

- Frameless, 1/4" (6 mm) thick Clear tempered glass
- Low, 1 3/4" (44 mm) threshold for easy entry and exit
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)
- 1" (25 mm) width adjustability on each wall jamb, offering 2" (51 mm) total adjustability

Technology

- Magnetic seal keeps door firmly closed, providing excellent water containment
- Knob handle keeps the design line simple and unobstructed
- Preassembled frame and out-of-plumb adjustability for simple installation with no cutting

Installation

- Adjustable ball catch for reliable operation
- Door can be installed to open to the left or right to suit your bathroom layout
- Not for use in hospitality
- For residential use only

Optional Products/Accessories

1296811 Whiston™ Door Filler Jamb



Codes/Standards

ANSI Z97.1

CAN/CGSB-12.1

CPSC 16CFR 1201


STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.

Available Glass Options

Code	Description
G05	Clear

DISCONTINUED This product has been discontinued.



Technical Information

All product dimensions are nominal.

Base-To-Wall 1" (25 mm)

Radius – Max:

Notes

Install this product according to the installation instructions.

The vertical opening should be a minimum of 75" (1905 mm) to allow for installation clearance.