

Features

- Frameless, 1/4" (6mm) thick Clear tempered glass.

Technology

- Double rollers provide a smooth gliding action to give a quality feel for years to come.
- Magnetic seal keeps door firmly closed, providing excellent water containment.
- Knob handle keeps the design line simple and unobstructed.
- Low threshold (1-3/4-inch) for easy entry and exit.
- CleanCoat® nanotechnology provides a smooth, nonstick surface to help prevent buildup of water stains, bacteria and mildew on your glass, to make it easy to clean and keep it looking like new.
- Detachable bottom rollers for ease of cleaning.
- Pre-assembled frame and out-of-plumb adjustability for simple installation with no cutting.

Installation

- Door can be installed to open to the left or right to suit your bathroom layout.
- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

1296811 Whiston™ Door Filler Jamb
K-23723 Faucet cleaner

Included Components

Additional Components:
Hardware kit



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.



Color Code Description

	S	Silver
--	---	--------

Available Glass Options

Code Description

G05	Clear
-----	-------



Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - Min: 45-1/16" (1145 mm)

Opening Width - Max: 47-1/16" (1195 mm)

Walk-through - Min: 19-3/4" (501 mm)

Walk-through - Max: 19-3/4" (501 mm)

Base-To-Wall Radius 1" (25 mm)

– Max:

Glass thickness: 1/4" (6 mm)

Glass coating: CleanCoat®

Notes

Install this product according to the installation instructions.

The vertical opening should be a minimum of 75" (1905 mm) to allow for installation clearance.