

Features

- Frameless, 3/16" (5mm) thick Clear tempered glass.

Technology

- Swings in or out for easy access and cleaning.
- Square minimalist-style wall jamb.
- CleanCoat® nanotechnology provides a smooth, nonstick surface to help prevent buildup of water stains, bacteria and mildew on your glass, to make it easy to clean and keep it looking like new.
- Out-of-plumb adjustability for simple installation.

Installation

- Door can be installed to open to the left or right to suit your bathroom layout.
- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:

Hardware kit



Codes/Standards

ANSI Z97.1

CPSC 16CFR 1201


STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
-------	------	-------------

	S	Silver
--	---	--------

Available Glass Options

Code	Description
------	-------------

G05	Clear
-----	-------



Technical Information

All product dimensions are nominal.

Installation type: For bath installation

Opening Width - Min: 31-1/2" (800 mm)

Base-To-Wall Radius 1/2" (13 mm)

- Max:

Glass thickness: 3/16" (5 mm)

Glass coating: CleanCoat®

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 57" (1448 mm) to allow for installation clearance.