

### Features

- Frameless design emphasizes glass and creates a sleek, minimalist look.
- Center-guided mechanism for smooth, quiet sliding action and easy cleaning.
- ComforTrack® cushioned track enables you to sit, lean or kneel on the bottom track of the door to comfortably bathe children or clean the bathing space.
- Smooth, easy-to-clean wall jambs.
- Interior and exterior towel bars complete the look of this door.
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)

### Material

- Frameless, 1/4" (6 mm) thick tempered glass.
- Anodized aluminum prevents rust and corrosion.

### Installation

- Fits opening widths 54-3/8" - 59-3/8" (1381 - 1508 mm).
- Out-of-plumb adjustability simplifies installation.
- Door can be installed to open to the left or right to suit your bathroom layout.
- For residential use only.
- Not for use in hospitality.

### Recommended Products/Accessories

K-23723 Faucet cleaner

### Included Components

Additional Components:  
Hardware kit




### Codes/Standards


ANSI Z97.1  
CPSC 16CFR 1201

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	ADR	Anodized Deep Bronze
	ADR	Anodized Deep Bronze
	N	Nickel
	N	Nickel
	S	Silver
	S	Silver



**Technical Information**

All product dimensions are nominal.

- Installation type: For bath installation
- Opening style: Sliding/Bypass
- Opening Width - Min: 54-3/8" (1381 mm)
- Opening Width - Max: 59-3/8" (1508 mm)
- Walk-through - Min: 22-1/2" (572 mm)
- Walk-through - Max: 27-1/2" (698 mm)
- Base-To-Wall Radius - Max: 5/8" (16 mm)
- Glass thickness: 1/4" (6 mm)
- Glass coating: CleanCoat®

**Notes**

Install this product according to the installation guide.