

Features

- Frameless design emphasizes glass and creates a sleek, minimalist look.
- Center-guided mechanism for smooth, quiet sliding action and easy cleaning.
- ComforTrack® cushioned track enables you to sit, lean or kneel on the bottom track of the door to comfortably bathe children or clean the bathing space.
- Smooth, easy-to-clean wall jambs.
- Interior and exterior towel bars complete the look of this door.
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)

Material

- Frameless, 1/4" (6 mm) thick tempered glass.
- Anodized aluminum prevents rust and corrosion.

Installation

- Fits opening widths 42-5/8" - 47-5/8" (1083 - 1210 mm).
- Out-of-plumb adjustability simplifies installation.
- Door can be installed to open to the left or right to suit your bathroom layout.
- For residential use only.
- Not for use in hospitality.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:
Hardware kit




Codes/Standards


ANSI Z97.1
CPSC 16CFR 1201

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	ADR	Anodized Deep Bronze
	ADR	Anodized Deep Bronze
	N	Nickel
	N	Nickel
	S	Silver
	S	Silver



***Walk-through**

Technical Information

All product dimensions are nominal.

- Installation type: For shower base installation, For shower base installation
- Opening style: Sliding/Bypass
- Opening Width - Min: 42-5/8" (1083 mm)
- Opening Width - Max: 47-5/8" (1210 mm)
- Walk-through - Min: 16-3/4" (425 mm)
- Walk-through - Max: 21-3/4" (552 mm)
- Base-To-Wall Radius - Max: 5/8" (16 mm)
- Glass thickness: 1/4" (6 mm)
- Glass coating: CleanCoat®

Notes

Install this product according to the installation guide.