

Features

- Frameless design emphasizes glass and creates a sleek, minimalist look.
- Center-guided mechanism for smooth, quiet sliding action and easy cleaning.
- ComforTrack™ enables you to sit, lean or kneel on the bottom track of the door to easily bathe children or clean the bathing space.
- Smooth, easy-to-clean wall jambs.
- CleanCoat® nanotechnology provides a smooth, nonstick surface to help prevent buildup of water stains, bacteria and mildew on your glass, to make it easy to clean and keep it looking like new.

Material

- Frameless, 1/4" (6 mm) thick tempered glass.
- Anodized aluminum prevents rusting and corrosion.

Technology

- Inside and outside towel bars complete the look of this door.

Installation

- Fits opening widths 54-3/8" – 59-3/8".
- Out-of-plumb adjustability allows for simpler installation.
- Door can be installed to open to the left or right to suit your bathroom layout.
- For residential use only.
- Not for use in hospitality.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:
Hardware kit



Codes/Standards


ANSI Z97.1
CPSC 16CFR 1201

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	ADR	Anodized Deep Bronze
	N	Nickel
	S	Silver



Technical Information

All product dimensions are nominal.
 Installation type: For shower base installation
 Opening style: Sliding/Bypass
 Opening Width - Min: 54-3/8" (1381 mm)
 Opening Width - Max: 59-3/8" (1508 mm)
 Walk-through - Min: 22-1/2" (572 mm)
 Walk-through - Max: 27-1/2" (699 mm)
 Base-To-Wall Radius 5/8" (16 mm)
 - Max:
 Glass thickness: 1/4" (6 mm)
 Glass coating: CleanCoat®

Notes

Install this product according to the installation guide.