

Features

- Frameless design emphasizes glass and creates a sleek, minimalist look.
- Center-guided mechanism for smooth, quiet sliding action and easy cleaning.
- ComforTrack® cushioned track enables you to sit, lean or kneel on the bottom track of the door to comfortably bathe children or clean the bathing space.
- Smooth, easy-to-clean wall jambs.
- Interior and exterior towel bars complete the look of this door.
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)

Material

- Frameless, 1/4" (6 mm) thick tempered glass.
- Anodized aluminum prevents rust and corrosion.

Installation

- Fits opening widths 54-3/8" - 59-3/8" (1381 - 1508 mm).
- Out-of-plumb adjustability simplifies installation.
- Door can be installed to open to the left or right to suit your bathroom layout.
- For residential use only.
- Not for use in hospitality.

Included Components

Additional Components:
Hardware kit




Codes/Standards


ANSI Z97.1
CPSC 16CFR 1201

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|---|------|----------------------|
|  | ADR | Anodized Deep Bronze |
|  | ADR | Anodized Deep Bronze |
|  | N | Nickel |
|  | N | Nickel |
|  | S | Silver |
|  | S | Silver |



Technical Information

All product dimensions are nominal.

| | |
|----------------------------|------------------------------|
| Installation type: | For shower base installation |
| Opening style: | Sliding/Bypass |
| Opening Width - Min: | 54-3/8" (1381 mm) |
| Opening Width - Max: | 59-3/8" (1508 mm) |
| Walk-through - Min: | 22-1/2" (572 mm) |
| Walk-through - Max: | 27-1/2" (699 mm) |
| Base-To-Wall Radius - Max: | 5/8" (16 mm) |
| Glass thickness: | 1/4" (6 mm) |
| Glass coating: | CleanCoat® |

Notes

Install this product according to the installation guide.