

## Features

- Frameless design emphasizes glass and creates a sleek, minimalist look
- Center-guided mechanism for smooth, quiet sliding action and easy cleaning
- ComforTrack® cushioned track enables you to sit, lean or kneel on the bottom track of the door to comfortably bathe children or clean the bathing space
- Smooth, easy-to-clean wall jambs
- Interior and exterior towel bars complete the look of this door
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)

## Material

- Frameless, 1/4" (6 mm) thick tempered glass
- Anodized aluminum prevents rust and corrosion

## Installation

- Fits opening widths 54-3/8" - 59-3/8" (1381 - 1508 mm)
- Out-of-plumb adjustability simplifies installation
- Door can be installed to open to the left or right to suit your bathroom layout
- For residential use only
- Not for use in hospitality



## Codes/Standards

ANSI Z97.1  
CAN/CGSB-12.1  
CPSC 16CFR 1201


## STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	ADR	Anodized Deep Bronze
	ADR	Anodized Deep Bronze
	N	Nickel
	N	Nickel
	S	Silver
	S	Silver



### Technical Information

All product dimensions are nominal.

Base-To-Wall 5/8" (16 mm)

Radius – Max:

Shower Ledge Min 2-1/2" (64 mm)

Flat:

Shower Wall Min 2-1/2" (64 mm)

Flat:

### Notes

Install this product according to the installation guide.