



# Deluxe Framed Sliding Bath Door 5900-57

## Features

- Framed
- 1/8" glass
- Towel bar
- Out-of-plumb adjustability
- Tempered glass ensures maximum safety and durability
- Anodized aluminum prevents rusting and corrosion

## Installation

- Not for use in hospitality.
- For residential use only.

## Included Components

Additional Components:  
Hardware kit



## Codes/Standards

ANSI Z97.1  
CPSC 16CFR 1201

## STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*


Color	Code	Description
-------	------	-------------

	S	
--	---	--

## Available Glass Options

Code	Description
------	-------------

	Pebbled
--	---------



**Technical Information**

All product dimensions are nominal.  
 Installation type: For bath installation  
 Opening Width - Min: 52-3/4" (1340 mm)  
 Opening Width - Max: 57-3/4" (1467 mm)  
 Walk-through - Min: 22-3/4" (578 mm)  
 Walk-through - Max: 27-3/4" (705 mm)  
 Glass thickness: 1/8" (3 mm)

**Notes**

Install this product according to the installation guide.  
 The vertical opening should be a minimum of 57-3/4" (1467 mm) to allow for installation clearance.