



Deluxe

Framed sliding bath door
5900-57

Features

- Framed, 1/8" (3 mm) thick tempered glass
- Towel bar
- Tempered glass ensures enhanced safety and durability

Material

- Anodized aluminum prevents rust and corrosion

Installation

- Out-of-plumb adjustability simplifies installation
- Not for use in hospitality
- For residential use only

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:

Hardware kit



Codes/Standards

ANSI Z97.1

CPSC 16CFR 1201


STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Glass Options

Code	Description
------	-------------

	Pebbled
--	---------



Technical Information

All product dimensions are nominal.

- Installation type: For bath installation
- Opening Width - Min: 52-3/4" (1340 mm)
- Opening Width - Max: 57-3/4" (1467 mm)
- Walk-through - Min: 22-3/4" (578 mm)
- Walk-through - Max: 27-3/4" (705 mm)
- Base-To-Wall Radius - Max: 1/2" (13 mm)
- Glass thickness: 1/8" (3 mm)

Notes

- Install this product according to the installation guide.
- The vertical opening should be a minimum of 57-11/16" (1465 mm) to allow for installation clearance.