



Deluxe Framed sliding bath door 5905-57

Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Towel bar.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

Installation

- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:
Hardware kit



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------




N	Nickel
---	--------

Available Glass Options

Code	Description
------	-------------

	Rain
--	------



Technical Information

All product dimensions are nominal.
 Installation type: For bath installation
 Opening Width - Min: 52-3/4" (1340 mm)
 Opening Width - Max: 57-3/4" (1467 mm)
 Walk-through - Min: 22-3/4" (578 mm)
 Walk-through - Max: 27-3/4" (705 mm)
 Base-To-Wall Radius 1/2" (13 mm)
 – Max:
 Glass thickness: 1/8" (3 mm)

Notes

Install this product according to the installation guide.
 The vertical opening should be a minimum of 57-11/16" (1465 mm) to allow for installation clearance.