



# Deluxe Framed sliding bath door 5905-57

## Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Towel bar.
- Tempered glass ensures maximum safety and durability.

## Material

- Anodized aluminum prevents rust and corrosion.

## Installation

- Out-of-plumb adjustability simplifies installation.
- Not for use in hospitality.
- For residential use only.

## Recommended Products/Accessories

K-23723 Faucet cleaner

## Included Components

Additional Components:

Hardware kit



## Codes/Standards

ANSI Z97.1

CPSC 16CFR 1201

## STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------



N	Nickel
---	--------

## Available Glass Options

Code	Description
------	-------------


	Rain
--	------

---

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).



**Technical Information**

All product dimensions are nominal.

- Installation type: For bath installation
- Opening Width - Min: 52-3/4" (1340 mm)
- Opening Width - Max: 57-3/4" (1467 mm)
- Walk-through - Min: 22-3/4" (578 mm)
- Walk-through - Max: 27-3/4" (705 mm)
- Base-To-Wall Radius - Max: 1/2" (13 mm)
- Glass thickness: 1/8" (3 mm)

**Notes**

- Install this product according to the installation guide.
- The vertical opening should be a minimum of 57-11/16" (1465 mm) to allow for installation clearance.