



Deluxe

Framed sliding bath door

5905-59

Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Towel bar.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

Installation


- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:
Hardware kit



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------



N	Nickel
---	--------



S	Silver
---	--------

Available Glass Options

Code	Description
------	-------------

	Birchwood®
--	------------


	Templar™
--	----------

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

4-25-2020 06:08 - US/CA



Technical Information

All product dimensions are nominal.
 Installation type: For bath installation
 Opening Width - Min: 54-3/8" (1381 mm)
 Opening Width - Max: 59-3/8" (1508 mm)
 Walk-through - Min: 23-9/16" (598 mm)
 Walk-through - Max: 28-9/16" (725 mm)
 Base-To-Wall Radius 1/2" (13 mm)
 - Max:
 Glass thickness: 1/8" (3 mm)

Notes

Install this product according to the installation guide.
 The vertical opening should be a minimum of 57-11/16" (1465 mm) to allow for installation clearance.