



Deluxe

Framed sliding bath door, 56-1/4" H x 59-3/8" W

5906-59

Features

- 1/8" (3 mm) thick tempered and fully framed Rain glass ensures maximum safety and durability
- Bypass system allows for easy access and suits your bathroom layout whether your showerhead is on the right or left
- Reversible top track and towel bar allow a choice between rounded or accented design
- Continuous bottom track guide system for smooth, quiet, and stable operation
- Made in the U.S.A

Material

- Anodized aluminum prevents rust and corrosion

Installation

- Fits opening widths 54-3/8" - 59-3/8" (1381 - 1508 mm)
- Requires 2" (51 mm) minimum threshold depth
- Out-of-plumb adjustability simplifies installation
- For residential use only
- Not for use in hospitality



Codes/Standards

ANSI Z97.1
CAN/CGSB-12.1
CPSC 16CFR 1201


STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
-------	------	-------------

	S	Silver
---	---	--------

Available Glass Options

Code	Description
------	-------------

G06	Rain
-----	------



Technical Information

All product dimensions are nominal.

Base-To-Wall	1/2" (13 mm)
Radius – Max:	
Shower Ledge Min	1-7/8" (48 mm)
Flat:	
Shower Wall Min	2-5/16" (59 mm)
Flat:	

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 57-11/16" (1465 mm) to allow for installation clearance.