



Deluxe

Framed sliding bath door

5935-56

Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Towel bar.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

Installation


- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:
Hardware kit



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201


STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|-------|------|-------------|
|-------|------|-------------|

| | | |
|--|---|--------|
|  | S | Silver |
|--|---|--------|

Available Glass Options

| Code | Description |
|------|-------------|
|------|-------------|


| | |
|--|------|
| | Rain |
|--|------|

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

4-25-2020 06:09 - US/CA



Technical Information

All product dimensions are nominal.

Installation type: For bath installation

Opening Width - Min: 51-1/4" (1302 mm)

Opening Width - Max: 56-1/4" (1429 mm)

Walk-through - Min: 22" (559 mm)

Walk-through - Max: 27" (686 mm)

Base-To-Wall Radius 1/2" (13 mm)

– Max:

Glass thickness: 1/8" (3 mm)

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 56-11/16" (1440 mm) to allow for installation clearance.