



# Deluxe

Framed sliding shower door  
**5960-43**

## Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Towel bar.
- Tempered glass ensures enhanced safety and durability.

## Material

- Anodized aluminum prevents rust and corrosion.

## Installation

- Out-of-plumb adjustability simplifies installation.
- Not for use in hospitality.
- For residential use only.

## Recommended Products/Accessories

K-23723 Faucet cleaner

## Included Components

Additional Components:

Hardware kit



## Codes/Standards

ANSI Z97.1

CPSC 16CFR 1201


## STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

## Available Glass Options

Code	Description
------	-------------

	Pebbled
--	---------



**Technical Information**

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - 37-1/2" (953 mm)  
Min:

Opening Width - 42-1/2" (1080 mm)  
Max:

Walk-through - Min: 15-1/8" (384 mm)

Walk-through - Max: 20-1/8" (511 mm)

Base-To-Wall 1/2" (13 mm)

Radius – Max:

Glass thickness: 1/8" (3 mm)

**Notes**

Install this product according to the installation guide.

The vertical opening should be a minimum of 66-15/16" (1700 mm) to allow for installation clearance.