

### Features

- Framed, 1/8" (3 mm) thick tempered glass
- Towel bar
- Tempered glass ensures enhanced safety and durability

### Material

- Anodized aluminum prevents rust and corrosion

### Installation

- Out-of-plumb adjustability simplifies installation
- Not for use in hospitality
- For residential use only



### Codes/Standards

ANSI Z97.1  
CAN/CGSB-12.1  
CPSC 16CFR 1201


### STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*


Color	Code	Description
-------	------	-------------

	S	Silver
---	---	--------

### Available Glass Options

Code	Description
------	-------------

	Pebbled
--	---------



**Technical Information**

All product dimensions are nominal.

- Base-To-Wall 1/2" (13 mm)
- Radius – Max:
- Shower Ledge Min 1-7/8" (48 mm)
- Flat:
- Shower Wall Min 2-5/16" (59 mm)
- Flat:

**Notes**

- Install this product according to the installation guide.
- The vertical opening should be a minimum of 66-15/16" (1700 mm) to allow for installation clearance.