



# Deluxe

## Framed sliding shower door

### 5960-55

#### Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Towel bar.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

#### Installation

- Not for use in hospitality.
- For residential use only.

#### Recommended Products/Accessories

K-23723 Faucet cleaner

#### Included Components

Additional Components:  
Hardware kit



#### Codes/Standards

ANSI Z97.1  
CPSC 16CFR 1201


#### STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

#### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	S	Silver
--	---	--------

#### Available Glass Options

Code	Description
------	-------------

	Pebbled
--	---------


---

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

4-25-2020 06:09 - US/CA



**Technical Information**

All product dimensions are nominal.  
 Installation type: For shower base installation  
 Opening Width - Min: 49-1/2" (1257 mm)  
 Opening Width - Max: 54-1/2" (1384 mm)  
 Walk-through - Min: 21-1/8" (537 mm)  
 Walk-through - Max: 26-1/8" (664 mm)  
 Base-To-Wall Radius 1/2" (13 mm)  
 - Max:  
 Glass thickness: 1/8" (3 mm)

**Notes**

Install this product according to the installation guide.  
 The vertical opening should be a minimum of 66-15/16" (1700 mm) to allow for installation clearance.