



Deluxe

Framed sliding shower door

5970-48

Features

- One of Sterling's most popular door series.
- Framed style.
- Reversible top track and towel bar.
- Smooth, quiet operation.

Installation

- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:

Hardware kit



Codes/Standards

ANSI Z97.1

CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|-------|------|-------------|
|-------|------|-------------|



| | |
|---|--------|
| S | Silver |
|---|--------|

Available Glass Options

| Code | Description |
|------|-------------|
|------|-------------|


| | |
|--|---------|
| | Pebbled |
|--|---------|

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

4-25-2020 06:10 - US/CA



Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - Min: 43-7/8" (1114 mm)

Opening Width - Max: 48-7/8" (1241 mm)

Walk-through - Min: 18-5/16" (465 mm)

Walk-through - Max: 23-5/16" (592 mm)

Base-To-Wall Radius 1/2" (13 mm)

- Max:

Glass thickness: 1/8" (3 mm)

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 71-3/8" (1813 mm) to allow for installation clearance.