

Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Towel bar.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

Installation

- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:
Hardware kit



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201



STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes


Color tiles intended for reference only.

Color Code Description

	N	Nickel
	S	Silver

Available Glass Options

Code	Description
	Birchwood®
	Ellipse
	Rain
	Templar™



Technical Information

All product dimensions are nominal.
 Installation type: For shower base installation
 Opening Width - Min: 54-3/8" (1381 mm)
 Opening Width - Max: 59-3/8" (1508 mm)
 Walk-through - Min: 23-9/16" (598 mm)
 Walk-through - Max: 28-9/16" (725 mm)
 Base-To-Wall Radius 1/2" (13 mm)
 - Max:
 Glass thickness: 1/8" (3 mm)

Notes

Install this product according to the installation guide.
 The vertical opening should be a minimum of 71-3/8" (1813 mm) to allow for installation clearance.