



Deluxe

Framed sliding shower door

5975-59

Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Towel bar.
- Tempered glass ensures maximum safety and durability.

Material

- Anodized aluminum prevents rust and corrosion.

Installation

- Out-of-plumb adjustability simplifies installation.
- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:

Hardware kit



Codes/Standards

ANSI Z97.1

CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|-------|------|-------------|
|-------|------|-------------|



| | |
|---|--------|
| N | Nickel |
|---|--------|



| | |
|---|--------|
| N | Nickel |
|---|--------|



| | |
|---|--------|
| N | Nickel |
|---|--------|



| | |
|---|--------|
| S | Silver |
|---|--------|



| | |
|---|--------|
| S | Silver |
|---|--------|

Available Glass Options

| Code | Description |
|------|-------------|
|------|-------------|

| | |
|--|------------|
| | Birchwood® |
|--|------------|

| | |
|--|---------|
| | Ellipse |
|--|---------|

| | |
|--|------|
| | Rain |
|--|------|


| | |
|--|----------|
| | Templar™ |
|--|----------|

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

5-29-2021 07:05 - US//CA



Technical Information

All product dimensions are nominal.

- Installation type: For shower base installation
- Opening Width - Min: 54-3/8" (1381 mm)
- Opening Width - Max: 59-3/8" (1508 mm)
- Walk-through - Min: 23-9/16" (598 mm)
- Walk-through - Max: 28-9/16" (725 mm)
- Base-To-Wall Radius - Max: 1/2" (13 mm)
- Glass thickness: 1/8" (3 mm)

Notes

- Install this product according to the installation guide.
- The vertical opening should be a minimum of 71-3/8" (1813 mm) to allow for installation clearance.