



Deluxe

Framed sliding shower door

5977-59

Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Towel bar.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

Installation

- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:
Hardware kit



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201


STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|-------|------|-------------|
|-------|------|-------------|

| | | |
|--|---|--------|
|  | S | Silver |
|--|---|--------|

Available Glass Options

| Code | Description |
|------|-------------|
|------|-------------|


| | |
|--|---------|
| | Ellipse |
|--|---------|

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

4-25-2020 06:11 - US/CA



Technical Information

All product dimensions are nominal.
 Installation type: For shower base installation
 Opening Width - Min: 54-3/8" (1381 mm)
 Opening Width - Max: 59-3/8" (1508 mm)
 Walk-through - Min: 23-9/16" (598 mm)
 Walk-through - Max: 28-9/16" (725 mm)
 Base-To-Wall Radius 1/2" (13 mm)
 – Max:
 Glass thickness: 1/8" (3 mm)

Notes

Install this product according to the installation guide.
 The vertical opening should be a minimum of 71-3/8" (1813 mm) to allow for installation clearance.