



All Pro® Performa™

60" x 30" Vikrell® bath/shower, right drain
61040120



Features

- 15" (381 mm) apron
- Tongue-and-groove walls with snap-together installation
- Lightly textured swirl-gloss finish
- Full caulking required in all seams
- Four shelves, 18" towel bar

Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

Installation

- Alcove
- Right drain

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23733 Vikrell® cleaner




Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73
- IAPMO Certification

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

- Drain location: Right
- Basin area, bottom: 48" x 21" (1219 mm x 533 mm)
- Basin area, top: 55" x 23" (1397 mm x 584 mm)
- Water depth: 9-3/8" (238 mm)
- Water capacity: 35 gal (132.5 L)
- Maximum door height: 57-3/4" (1467 mm)
- Maximum door width: 57-1/2" (1461 mm)

Notes

- Install this product according to the installation instructions.
- Studs should be positioned roughly as shown.
- Double studding is recommended for pivot shower door installations.