

### Features

- Frameless.
- 1/4" (6 mm) thick tempered glass.
- CleanCoat®+ glass coating creates a hydrophobic barrier that repels water, soap scum, and residue, saving time and protecting shower doors 10 times longer than original CleanCoat. (Based on 2021 internal wear/abrasion testing using a microfiber cloth.)
- Knob handle.

### Material

- Anodized aluminum prevents rust and corrosion.

### Technology

- Tempered glass ensures maximum safety and durability.

### Installation

- Out-of-plumb adjustability simplifies installation.
- Not for use in hospitality.
- For residential use only.

### Included Components

Additional Components:  
Hardware kit



### Codes/Standards

ANSI Z97.1  
CPSC 16CFR 1201


### STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

### Available Glass Options

Code	Description
	Clear
	Frosted

**DISCONTINUED** This product has been discontinued.



**Technical Information**

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - Min: 32-1/2" (826 mm)

Opening Width - Max: 34" (864 mm)

Walk-through - Min: 26-3/4" (679 mm)

Walk-through - Max: 28-1/4" (718 mm)

Glass thickness: 1/4" (6 mm)

Glass coating: CleanCoat®

**Notes**

Install this product according to the installation guide.

The vertical opening should be a minimum of 66" (1676 mm) to allow for installation clearance.