

**Features**

- Frameless.
- 1/4" (6 mm) thick tempered glass.
- Knob handle.

**Technology**

- CleanCoat® nanotechnology provides a smooth, nonstick surface to help prevent buildup of water stains, bacteria and mildew on your glass, to make it easy to clean and keep it looking like new.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

**Installation**

- Not for use in hospitality.
- For residential use only.

**Included Components**

Additional Components:  
Hardware kit



**Codes/Standards**

ANSI Z97.1  
CPSC 16CFR 1201

**STERLING® Warranty - Bath and Shower Doors**


See website for detailed warranty information.

**Available Glass Options**

Code Description

Clear

**DISCONTINUED** This product has been discontinued.



**Technical Information**

All product dimensions are nominal.  
 Installation type: For shower base installation  
 Opening Width - Min: 35" (889 mm)  
 Opening Width - Max: 36-1/2" (927 mm)  
 Walk-through - Min: 29-1/4" (743 mm)  
 Walk-through - Max: 30-3/4" (781 mm)  
 Glass thickness: 1/4" (6 mm)  
 Glass coating: CleanCoat®

**Notes**

Install this product according to the installation guide.  
 The vertical opening should be a minimum of 66" (1676 mm) to allow for installation clearance.