

Features

- Frameless.
- 1/4" (6 mm) thick tempered glass.
- Knob handle.

Technology

- CleanCoat® nanotechnology provides a smooth, nonstick surface to help prevent buildup of water stains, bacteria and mildew on your glass, to make it easy to clean and keep it looking like new.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

Installation

- Not for use in hospitality.
- For residential use only.

Included Components

Additional Components:
Hardware kit

Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors


See website for detailed warranty information.

Available Glass Options

Code	Description
------	-------------

	Clear
--	-------

DISCONTINUED This product has been discontinued.



Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - Min: 37-1/2" (953 mm)

Opening Width - Max: 39" (991 mm)

Walk-through - Min: 31-3/4" (806 mm)

Walk-through - Max: 33-1/4" (845 mm)

Glass thickness: 1/4" (6 mm)

Glass coating: CleanCoat®

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 66" (1676 mm) to allow for installation clearance.