



Finesse™

Framed pivot shower door

6505-33

Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Exterior towel bar.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

Installation

- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:
Hardware kit



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201


STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	DR	Deep Bronze
--	----	-------------

Available Glass Options

Code	Description
------	-------------


	Rain
--	------

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

3-22-2020 07:12 - US/CA



Technical Information

All product dimensions are nominal.
 Installation type: For shower base installation
 Opening Width - Min: 30-1/2" (775 mm)
 Opening Width - Max: 33-1/2" (851 mm)
 Walk-through - Min: 25-7/16" (646 mm)
 Walk-through - Max: 28-7/16" (722 mm)
 Base-To-Wall Radius 1/2" (13 mm)
 – Max:
 Glass thickness: 1/8" (3 mm)

Notes

Install this product according to the installation guide.
 The vertical opening should be a minimum of 66" (1676 mm) to allow for installation clearance.