



# Finesse™

## Framed pivot shower door

### 6505-36

#### Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Exterior towel bar.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

#### Installation

- Not for use in hospitality.
- For residential use only.

#### Recommended Products/Accessories

K-23723 Faucet cleaner

#### Included Components

Additional Components:  
Hardware kit



#### Codes/Standards

ANSI Z97.1  
CPSC 16CFR 1201


#### STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

#### Available Colors/Finishes

*Color tiles intended for reference only.*


Color	Code	Description
-------	------	-------------

	DR	Deep Bronze
--	----	-------------

#### Available Glass Options

Code	Description
------	-------------

	Rain
--	------



**Technical Information**

- All product dimensions are nominal.
- Installation type: For shower base installation
- Opening Width - Min: 33" (838 mm)
- Opening Width - Max: 36" (914 mm)
- Walk-through - Min: 27-15/16" (710 mm)
- Walk-through - Max: 30-15/16" (786 mm)
- Base-To-Wall Radius 1/2" (13 mm)
- Max:
- Glass thickness: 1/8" (3 mm)

**Notes**

- Install this product according to the installation guide.
- The vertical opening should be a minimum of 66" (1676 mm) to allow for installation clearance.