



Finesse™
Framed pivot shower door
6506-33

Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Exterior towel bar.
- Tempered glass ensures maximum safety and durability.

Material

- Anodized aluminum prevents rust and corrosion.

Installation

- Out-of-plumb adjustability simplifies installation.
- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:

Hardware kit



Codes/Standards

ANSI Z97.1

CPSC 16CFR 1201

DISCONTINUED **STERLING® Warranty - Bath and Shower Doors** product has been discontinued.


See website for detailed warranty information.

Available Glass Options

Code Description

Rain

DISCONTINUED This product has been discontinued.



Technical Information

All product dimensions are nominal.

- Installation type: For shower base installation
- Opening Width - Min: 30-1/2" (775 mm)
- Opening Width - Max: 33-1/2" (851 mm)
- Walk-through - Min: 25-7/16" (646 mm)
- Walk-through - Max: 28-7/16" (722 mm)
- Base-To-Wall Radius - Max: 1/2" (13 mm)
- Glass thickness: 1/8" (3 mm)

Notes

- Install this product according to the installation guide.
- The vertical opening should be a minimum of 66" (1676 mm) to allow for installation clearance.