

### Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Exterior towel bar.
- Tempered glass ensures enhanced safety and durability.

### Material

- Anodized aluminum prevents rust and corrosion.

### Installation

- Out-of-plumb adjustability simplifies installation.
- Not for use in hospitality.
- For residential use only.

### Recommended Products/Accessories

K-23723 Faucet cleaner

### Included Components

Additional Components:

Hardware kit



### Codes/Standards

ANSI Z97.1

CPSC 16CFR 1201

This product has been discontinued.

### STERLING® Warranty - Bath and Shower Doors


See website for detailed warranty information.

### Available Glass Options

Code	Description
------	-------------

	Rain
--	------

**DISCONTINUED** This product has been discontinued.



### Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - Min: 36-1/2" (927 mm)

Opening Width - Max: 39-1/2" (1003 mm)

Walk-through - Min: 31-7/16" (799 mm)

Walk-through - Max: 34-7/16" (875 mm)

Base-To-Wall Radius - Max: 1/2" (13 mm)

Glass thickness: 1/8" (3 mm)

### Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 66" (1676 mm) to allow for installation clearance.