



Performa™

60" x 29" Vikrell® bath, left above-floor drain

71041112



Features

- Durable high-gloss finish
- 17-1/4" (438 mm) bath depth (floor to top of threshold)
- 60" (1524 mm) x 29" (737 mm) x 17-1/4" (438 mm) complete unit finished dimensions

Material

- Compression molded from our exclusive solid Vikrell® material

Installation

- Above-floor-drain (AFD) rough-in

Recommended Products/Accessories

K-23726 Drain treatment
K-23733 Vikrell® cleaner



ADA

Codes/Standards

CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
ADA
ICC/ANSI A117.1
HUD, UM Bulletin 73
IAPMO Certification


STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|-------|------|-------------|
|-------|------|-------------|


| | | |
|---|---|-------|
|  | 0 | White |
|---|---|-------|

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

3-23-2024 21:07 - US



Technical Information

All product dimensions are nominal.

| | |
|---------------------|------------------------------|
| Drain location: | Left |
| Basin area, bottom: | 21" x 39" (533 mm x 991 mm) |
| Basin area, top: | 24" x 53" (610 mm x 1346 mm) |
| Water depth: | 9-3/4" (248 mm) |
| Water capacity: | 35 gal (132.5 L) |
| Maximum door width: | 56-3/4" (1441 mm) |

Notes

Install this product according to the installation instructions.

Studs should be positioned roughly as shown.

Double studding is recommended for pivot shower door installations.

ADA compliant when installed to the specific requirements of these regulations.