



# Accord® 60" x 32" bath/shower with AIP grab bars 71150113-V



## Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction.
- Integral apron.
- Realistic tile pattern with convenient shelves for ample storage.
- Easy-to-clean, durable high-gloss finish.
- Includes three Aging in Place Matte Silver grab bars (one 80012134 and two 80001024).

## Material

- Compression molded from our exclusive solid Vikrell® material.

## Installation

- Alcove.
- Caulk-free installation.
- Left drain.



## Recommended Products/Accessories

- 5425-57 Frameless sliding bath door
- 5425-59 Frameless sliding bath door
- 5427-59 Frameless sliding bath door
- 542808-59 Frameless sliding bath door
- 71157103 32" bath/shower grab bar kit
- 1095008 Plastic Seat
- K-23726 Drain treatment
- K-23723 Faucet cleaner
- K-23733 Vikrell® cleaner

## Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73

## Warranty – Bathing Fixtures (and) Kitchen and Utility Sinks Made of Solid Vikrell® Material Warranty - Grab Bars


See website for detailed warranty information.

## Included Components

Product consists of:

- 71151110 60-1/4" x 32" bath
- 71154103-V 60" wall set w/ AIP grab bars

**DISCONTINUED** This product has been discontinued.



**Technical Information**

All product dimensions are nominal.

Installation:	Three-wall alcove
Drain location:	Left
Basin area, bottom:	21-1/2" x 46-1/8" (546 mm x 1172 mm)
Basin area, top:	23" x 51" (584 mm x 1295 mm)
Water depth:	13-1/8" (333 mm)
Water capacity:	56 gal (212 L)
Maximum door height:	55-7/8" (1419 mm)
Maximum door width:	56-3/4" (1441 mm)

**Notes**

- Install this product according to the installation instructions.
- Studs should be positioned roughly as shown. Double studding is recommended for pivot shower door installations.
- Bath cannot be installed without the wall surround.
- Attach grab bars at the specified backerboard locations only.