



**Accord®**

60" wall set with Aging in Place grab bars  
**71154103-N**



### Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction.
- Realistic tile pattern with convenient shelves for ample storage.
- Easy to clean, durable high-gloss finish.
- Includes three Aging in Place Nickel grab bars (one 80012134 and two 80001024).
- Compatible with Accord bath 71151110 or 71151120.

### Material

- Compression molded from our exclusive solid Vikrell® material.

### Installation

- Alcove.
- Caulk-free installation.

### Required Products/Accessories

71151110 60" bath

or

71151120 60" bath


### Recommended Products/Accessories

5425-57 Frameless sliding bath door  
5425-59 Frameless sliding bath door  
5427-59 Frameless sliding bath door  
542808-59 Frameless sliding bath door  
71157103 32" bath/shower grab bar kit  
1095008 Plastic Seat  
K-23723 Faucet cleaner

### Included Components

Product consists of:

80012134 34" curved grab bar  
80001024 24" straight grab bar (Qty 2)



### Codes/Standards

CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662

### Warranty – Bathing Fixtures (and) Kitchen and Utility Sinks Made of Solid Vikrell® Material



#### STERLING® Warranty - Grab Bars

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

#### Color Code Description

	0	White
	96	KOHLER Biscuit

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

3-12-2020 11:50 - US



**Accord®**  
60" wall set with Aging in Place grab bars  
**71154103-N**

No image available.  
This product is a component and not intended to be a standalone installation.

**Technical Information**

All product dimensions are nominal.

Installation: Three-wall alcove

Maximum door height: 55" (1397 mm)

Maximum door width: 56-3/4" (1441 mm)

**Notes**

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.