



Accord®

60" wall set with Aging in Place grab bars
71154103-V



Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction.
- Realistic tile pattern with convenient shelves for ample storage.
- Easy to clean, durable high-gloss finish.
- Includes three Aging in Place Matte Silver grab bars (one 80012134 and two 80001024).
- Compatible with Accord bath 71151110 or 71151120.

Material

- Compression molded from our exclusive solid Vikrell® material.

Installation

- Alcove.
- Caulk-free installation.



Required Products/Accessories

71151110 60" bath

or

71151120 60" bath

Recommended Products/Accessories

5425-57 Frameless sliding bath door
5425-59 Frameless sliding bath door
5427-59 Frameless sliding bath door
542808-59 Frameless sliding bath door
71157103 32" bath/shower grab bar kit
1095008 Plastic Seat
K-23723 Faucet cleaner

Included Components

Product consists of:

80012134 34" curved grab bar
80001024 24" straight grab bar (Qty 2)

Codes/Standards

CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662



Warranty – Bathing Fixtures (and) Kitchen and Utility Sinks Made of Solid Vikrell® Material

STERLING® Warranty - Grab Bars

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	KOHLER Biscuit

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

3-12-2020 11:50 - US



Accord®
60" wall set with Aging in Place grab bars
71154103-V

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Installation: Three-wall alcove

Maximum door height: 55" (1397 mm)

Maximum door width: 56-3/4" (1441 mm)

Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.