



**Accord®**  
60-1/4" x 30" bath/shower with Aging in Place grab bars  
**71240113-V**



### Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Integral apron
- Convenient shelves provide generous storage space
- Easy-to-clean, durable high-gloss finish
- Includes three Aging in Place Matte Silver grab bars (one 80011032 and two 80001024)

### Material

- Compression molded from our exclusive solid Vikrell® material

### Installation

- Alcove
- Caulk-free installation
- Left drain

### Recommended Products/Accessories

5425-57 Frameless sliding bath door  
5425-59 Frameless sliding bath door  
5905-59 Framed sliding bath door  
5906-59 Framed sliding bath door, 56-1/4" H x 59-3/8" W  
542808-59 55-1/2" H frameless sliding bath door with 5/16"-thick glass  
581005-59 Frameless sliding bath door  
71247103 30" ADA adaptable smooth bath/shower grab bar kit  
71147104 30" bath seat kit  
K-23726 Drain treatment  
K-23723 Faucet cleaner  
K-23733 Vikrell® cleaner

### Included Components


71141110 60" x 30" Vikrell® bath, left drain

### Codes/Standards

CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662  
HUD, UM Bulletin 73  
IAPMO Certification

**STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty**  
**STERLING® Grab Bars Ten-Year Limited Warranty**

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Drain location:	Left
Basin area, bottom:	46-1/4" x 20-1/2" (1175 mm x 521 mm)
Basin area, top:	52-1/4" x 22-1/2" (1327 mm x 572 mm)
Water depth:	11" (279 mm)
Water capacity:	34 gal (128.7 L)
Minimum flat for door:	2-3/4" (70 mm)
Maximum door height:	56-1/2" (1435 mm)
Maximum door width:	56-3/4" (1441 mm)

## Notes

Install this product according to the installation instructions.

Product is designed to be used with a single-hole mixer valve with an escutcheon cover not to exceed 7-3/4" (197 mm) in width.

Studs should be positioned roughly as shown.

Double studding is recommended for pivot shower door installations.

Bath cannot be installed without the wall surround.

Attach grab bars at the specified backerboard locations only.

Width of back wall at top transitions from 60" (1524 mm) at the front to 59-3/8" (1508 mm) in the back corners. Furring strips approximately 1/4" (6 mm) thick should be used at the back corner studs if drywall is to be installed over the nailing flange.