



### Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Convenient shelves provide generous storage space
- Easy-to-clean, durable high-gloss finish
- Includes three Aging in Place Matte Silver grab bars (one 80011032 and two 80001024)
- Must be installed with Accord bath 71141110 or 71141120

### Material

- Compression molded from our exclusive solid Vikrell® material

### Installation

- Alcove
- Caulk-free installation



### Required Products/Accessories

- 71141110 60" x 30" Vikrell® bath, left drain
- or
- 71141120 60" x 30" Vikrell® bath, right drain

### Recommended Products/Accessories

- 5425-57 Frameless sliding bath door
- 5425-59 Frameless sliding bath door
- 5905-59 Framed sliding bath door
- 5906-59 Framed sliding bath door, 56-1/4" H x 59-3/8" W
- 542808-59 55-1/2" H frameless sliding bath door with 5/16"-thick glass
- 581005-59 Frameless sliding bath door
- 71247103 30" ADA adaptable smooth bath/shower grab bar kit
- 71147104 30" bath seat kit
- K-23723 Faucet cleaner
- K-23733 Vikrell® cleaner

### Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- IAPMO Certification

### STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty STERLING® Grab Bars Ten-Year Limited Warranty

See website for detailed warranty information.

### Included Components

- 80011032 32" straight grab bar
- 80001024 24" straight grab bar (Qty 2)

**DISCONTINUED** This product has been discontinued.

No image available.  
This product is a component and not intended to be a standalone installation.

**DISCONTINUED** This product has been discontinued.

### Technical Information

All product dimensions are nominal.

Maximum door height: 56-1/2" (1435 mm)

Maximum door width: 56-3/4" (1441 mm)

### Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.

**DISCONTINUED** This product has been discontinued.