



**Lawson®**  
72" x 42" Vikrell® drop-in bath  
**71311100**



**Features**

- 20" bath depth
- Durable high-gloss finish
- Reversible drain can be installed as left- or right-hand drain
- Optional flange kit available for easier conversion to alcove installation. Kit provides continuous rim support and added water containment benefits compared to nonflanged alcove installation

**Material**

- Made from solid Vikrell® material for strength, durability, and lasting beauty

**Installation**

- Drop-in

**Recommended Products/Accessories**

71317100 Tile-in flange kit for 72" soaking baths  
K-23726 Drain treatment  
K-23733 Vikrell® cleaner



**Codes/Standards**

CSA B45.5/IAPMO Z124  
ASTM E162  
ASTM E662  
HUD, UM Bulletin 73


**STERLING® Vikrell® or Acrylic Baths  
and Shower Bases Ten-Year Limited  
Warranty**


See website for detailed warranty information.

**Available Colors/Finishes**

*Color tiles intended for reference only.*

**Color Code Description**

	0	White
---	---	-------



### Technical Information

All product dimensions are nominal.

Drain location:	Reversible
Basin area, bottom:	50" x 25-5/8" (1270 mm x 651 mm)
Basin area, top:	59" x 33" (1499 mm x 838 mm)
Water depth:	15-1/4" (387 mm)
Water capacity:	80 gal (302.8 L)
Maximum door width:	72" (1829 mm)

### Notes

Install this product according to the installation instructions.

Double studding is recommended for pivot shower door installations.

Studs should be positioned roughly as shown.