



A KOHLER COMPANY

Intrigue™

39" tile neo-angle shower 72040100



Features

- 4-7/8" threshold.
- Durable high-gloss finish.
- Center drain.
- Two-piece, tongue-and-groove walls with snap-together installation.
- Three convenient shelves.

Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty.

Installation

- Alcove.
- Caulk required for proper installation.

Recommended Products/Accessories

- SP2270A-38 Framed neo-angle corner shower door
- SP2275A-38 Framed neo-angle corner shower door
- SP2276A-38 Framed neo-angle corner shower door
- SP2277A-38 Framed neo-angle corner shower door
- SP2375-38 Frameless neo-angle corner shower door
- 80001012 12" straight grab bar
- 80001018 18" straight grab bar
- 80001024 24" straight grab bar
- 80011032 32" straight grab bar
- 80001036 36" straight grab bar
- K-23726 Drain treatment
- K-23733 Vikrell® cleaner

Included Components

Product consists of:

- 72044100 39" tile neo-angle shower wall set
- 72041100 39" neo-angle shower base



Codes/Standards



- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662



Warranty – Bathing Fixtures (and) Kitchen and Utility Sinks Made of Solid Vikrell® Material

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	KOHLER Biscuit



Technical Information

All product dimensions are nominal.

- Installation: Corner
- Drain location: Center
- Minimum flat for door: 3" (76 mm)
- Threshold height: 4-7/8" (124 mm)
- Maximum door height: 74" (1880 mm)
- Maximum door width: 27-3/8" (695 mm)

Notes

- Install this product according to the installation instructions.
- Studs should be positioned roughly as shown.
- Double studding is recommended for pivot shower door installations.