



# Intrigue™

39" x 39" Vikrell® tile neo-angle shower stall, center drain  
72040100



### Features

- 4-7/8" threshold
- Durable high-gloss finish
- Two-piece tongue-and-groove walls with snap-together installation
- Three convenient shelves

### Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

### Installation

- Alcove
- Center drain
- Caulk required for proper installation

### Recommended Products/Accessories

- SP2276A-38 Framed neo-angle corner shower door
- 80001012 12" straight grab bar
- 80001018 18" straight grab bar
- 80001024 24" straight grab bar
- 80011032 32" straight grab bar
- 80001036 36" straight grab bar
- K-23726 Drain treatment
- K-23733 Vikrell® cleaner

### Included Components

- 72041100 39" x 39" Vikrell® neo-angle shower base, center drain





### Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- IAPMO Certification

### STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Drain location:	Center
Maximum door height:	74" (1880 mm)
Maximum door width:	27-3/8" (695 mm)

### Notes

Install this product according to the installation instructions.

Studs should be positioned roughly as shown.

Double studding is recommended for pivot shower door installations.