



# Intrigue™

39" x 39" Vikrell® tile neo-angle shower with Aging in Place backerboards, center drain  
**72040106**



## Features

- 4-7/8" threshold
- Durable high-gloss finish
- Two-piece tongue-and-groove walls with snap-together installation
- Three convenient shelves
- Aging in Place backerboards

## Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

## Installation

- Alcove
- Center drain
- Caulk required for proper installation

## Recommended Products/Accessories

- SP2276A-38 Framed neo-angle corner shower door
- 80001012 12" straight grab bar
- 80001018 18" straight grab bar
- 80001024 24" straight grab bar
- 80011032 32" straight grab bar
- 80001036 36" straight grab bar
- K-23726 Drain treatment
- K-23733 Vikrell® cleaner

## Included Components

- 72041100 39" x 39" Vikrell® neo-angle shower base, center drain




## Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662

## STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.



**Technical Information**

All product dimensions are nominal.

- Drain location: Center
- Maximum door height: 74" (1880 mm)
- Maximum door width: 15-7/8" (403 mm)

**Notes**

- Install this product according to the installation instructions.
- Attach grab bars at the specified backerboard locations only.
- Studs should be positioned roughly as shown. Double studding is recommended for pivot shower door installations.