



Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- 3-1/2" threshold
- Realistic tile pattern with convenient shelves for ample storage
- Easy-to-clean, durable high-gloss finish
- Includes two Aging in Place Nickel grab bars (two 80001024)

Material

- Compression molded from our exclusive solid Vikrell® material

Installation

- Alcove
- Caulk-free installation
- Center drain



Recommended Products/Accessories

- 1500D-42 Framed pivot shower door
- 1505D-42 Framed pivot shower door
- 1530D-42 Framed pivot shower door
- 1535D-42 Framed pivot shower door
- 5960-43 Framed sliding shower door
- K-23726 Drain treatment
- K-23723 Faucet cleaner
- K-23733 Vikrell® cleaner

Included Components

- Product consists of:
- 72252100
 - 72251100
 - 72245103-N


Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty
STERLING® Grab Bars Ten-Year Limited Warranty

See website for detailed warranty information.

DISCONTINUED This product has been discontinued.



Technical Information

All product dimensions are nominal.

Installation:	Three-wall alcove
Drain location:	Center
Maximum door height:	72" (1829 mm)
Maximum door width:	38-5/8" (981 mm)

Notes

- Install this product according to the installation instructions.
- Studs should be positioned roughly as shown. Double studding is recommended for pivot shower door installations.
- Attach grab bars at the specified backerboard locations only.
- Shower base cannot be installed without the wall surround.