



# Accord®

48-1/4" x 36" shower stall with Aging in Place grab bars

## 72260103-N



### Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- 3-1/2" threshold
- Geometric back wall design with convenient shelves for ample storage
- Easy-to-clean, durable high-gloss finish
- Includes three Aging in Place Nickel grab bars (one 80012031 and two 80001024)

### Material

- Compression molded from our exclusive solid Vikrell® material

### Installation


- Alcove
- Caulk-free installation
- Center drain

### Recommended Products/Accessories

- 1500D-48 Framed pivot shower door
- 5475-48 Frameless sliding shower door
- 5970-48 Framed sliding shower door
- 5975-48 Framed sliding shower door
- 5976-48 Framed sliding shower door
- 547808-48 Frameless sliding shower door
- 581075-48 Frameless sliding shower door
- K-23726 Drain treatment
- K-23723 Faucet cleaner
- K-23733 Vikrell® cleaner

### Included Components

- 72261100 48" x 36" Vikrell® shower base, center drain




### Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73
- IAPMO Certification

**STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty**  
**STERLING® Grab Bars Ten-Year Limited Warranty**

See website for detailed warranty information.



**Technical Information**

All product dimensions are nominal.

Drain location:	Center
Minimum flat for door:	3-1/4" (83 mm)
Maximum door height:	72" (1829 mm)
Maximum door width:	44-5/8" (1133 mm)

**Notes**

- Install this product according to the installation instructions.
- Studs should be positioned roughly as shown. Double studding is recommended for pivot shower door installations.
- Attach grab bars at the specified backerboard locations only.
- Shower base cannot be installed without the wall surround.