



Accord®

48" x 36" Vikrell® seated shower, center drain
72280100



Features

- 3-1/2" threshold
- Durable high-gloss finish
- Three-piece tongue-and-groove walls with snap-together installation
- Removable seat

Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

Installation

- Alcove
- Center drain
- Caulk-free installation

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23733 Vikrell® cleaner

Included Components

- 72281100 48" x 36" Vikrell® seated shower base, center drain
- 72284100 48" x 36" Vikrell® seated shower wall set



Codes/Standards

HUD, UM Bulletin 73
IAPMO Certification



STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White



Technical Information

All product dimensions are nominal.

Drain location:	Center
Weight:	123 lbs (55.8 kg)
Maximum door height:	70-5/8" (1794 mm)
Maximum door width:	44-5/8" (1133 mm)

Notes

Install this product according to the installation instructions.

Studs should be positioned roughly as shown.

Double studding is recommended for pivot shower door installations.

Base cannot be installed without the wall surround.