



Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Geometric back wall design with convenient shelves for ample storage
- Easy-to-clean, durable high-gloss finish
- Includes removable seat that can be positioned on either side of the shower base
- Includes three Aging in Place Nickel grab bars (one 80012222 and two 8001024)

Material

- Compression molded from our exclusive solid Vikrell® material

Installation


- Alcove
- Caulk-free installation
- Center drain

Recommended Products/Accessories

1500D-48 Framed pivot shower door
5475-48 Frameless sliding shower door
5970-48 Framed sliding shower door
5975-48 Framed sliding shower door
5976-48 Framed sliding shower door
547808-48 Frameless sliding shower door
581075-48 Frameless sliding shower door
72286104 Removable bath seat for Series 7228 and 7229
K-23726 Drain treatment
K-23723 Faucet cleaner
K-23733 Vikrell® cleaner

Included Components

72281100 48" x 36" Vikrell® seated shower base, center drain
72286104 Removable bath seat for Series 7228 and 7229
72286104 Removable bath seat for Series 7228 and 7229
72281100 48" x 36" Vikrell® seated shower base, center drain




Codes/Standards

CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
HUD, UM Bulletin 73
IAPMO Certification

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty
STERLING® Grab Bars Ten-Year Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Drain location:	Center
Minimum flat for door:	3-1/4" (83 mm)
Maximum door height:	70-5/8" (1794 mm)
Maximum door width:	44-5/8" (1133 mm)

Notes

Install this product according to the installation instructions.

Studs should be positioned roughly as shown.

Double studding is recommended for pivot shower door installations.

Base cannot be installed without the wall surround.