



# 48" x 34" x 75" Vikrell® shower with Aging in Place backerboards 72284103-N



## Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Geometric back wall design with convenient shelves for ample storage
- Easy-to-clean, durable high-gloss finish
- Includes three Aging in Place Nickel grab bars (one 80012222 and two 80001024)

## Material

- Compression molded from our exclusive solid Vikrell® material

## Installation


- Alcove
- Caulk-free installation

## Recommended Products/Accessories

- 1500D-48 Framed pivot shower door
- 5475-48 Frameless sliding shower door
- 5970-48 Framed sliding shower door
- 5975-48 Framed sliding shower door
- 5976-48 Framed sliding shower door
- 547808-48 Frameless sliding shower door
- 581075-48 Frameless sliding shower door
- 72286104 Removable bath seat for Series 7228 and 7229
- K-23723 Faucet cleaner
- K-23733 Vikrell® cleaner

## Included Components

- 80012222 22" curved grab bar
- 80001024 24" straight grab bar (Qty 2)






## Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- IAPMO Certification

## STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty STERLING® Grab Bars Ten-Year Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Drain location:	Center
Maximum door height:	70-5/8" (1794 mm)
Maximum door width:	44-5/8" (1133 mm)

### Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.