



Accord®

48" shower wall set with Aging in Place grab bars
72284103-V



Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction.
- Geometric back wall design with convenient shelves for ample storage.
- Easy to clean, durable high-gloss finish.
- Includes three Aging in Place Matte Silver grab bars (one 80012222 and two 80001024).

Material

- Compression molded from our exclusive solid Vikrell® material.

Installation

- Alcove.
- Caulk-free installation.



Recommended Products/Accessories

- 695B-48 Framed sliding shower door
- 1500D-48 Framed pivot shower door
- 1505D-48 Framed pivot shower door
- 1506D-48 Framed pivot shower door
- 1530D-48 Framed pivot shower door
- 1535D-48 Framed pivot shower door
- 5475-48 Frameless sliding shower door
- 5477-48 Frameless sliding shower door
- 5970-48 Framed sliding shower door
- 5975-48 Framed sliding shower door
- 5976-48 Framed sliding shower door
- 5977-48 Framed sliding shower door
- 547808-48 Frameless sliding shower door
- 572075-48 Framed sliding shower door
- 581075-48 Frameless sliding shower door
- 72286104 Removable bath seat for Series 7228 and 7229
- K-23723 Faucet cleaner

Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662

Warranty – Bathing Fixtures (and Kitchen and Utility Sinks Made of Solid Vikrell® Material)

STERLING® Warranty - Grab Bars
STERLING® Warranty - Bathing & Showering Seats

See website for detailed warranty information.

Included Components

Product consists of:

- 80012222 22" curved grab bar
- 80001024 24" straight grab bar (Qty 2)

Available Colors/Finishes

Color tiles intended for reference only.





Color	Code	Description
	0	White
	96	KOHLER Biscuit

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

3-12-2020 12:04 - US



Backer Board Locations

Technical Information

All product dimensions are nominal.
 Installation: Three-wall alcove
 Drain location: Center
 Maximum door height: 70-5/8" (1794 mm)
 Maximum door width: 44-5/8" (1133 mm)

Notes

Install this product according to the installation instructions.
 Measure your actual product for roughing-in details.